

CERTIFICATE OF ANALYSIS

PRODUCT: Corning® Matrigel® Basement Membrane Matrix High Concentration, Phenol Red Free, 10 ml vial

CATALOG NUMBER: 354262

LOT NUMBER: 9287013

SOURCE: Engelbreth-Holm-Swarm (EHS) Mouse Tumor

FORMULATION: Dulbecco's Modified Eagle's Medium with 50 µg/ml gentamycin

Corning Matrigel Matrix High Concentration is compatible with all culture media

STORAGE: Store at -20°C. Avoid multiple freeze-thaws. Do not store in frost-free freezer. **KEEP FROZEN.**


QUALITY CONTROL:

| Specification | Criteria | Result |
|-----------------------|---|----------|
| Protein Concentration | Results obtained by Lowry method and represented in mg/ml. | 19.63 |
| Endotoxin | Endotoxin units (EU)/ml are measured by Limulus Amoebocyte Lysate assay. | < 1.5 |
| Gelling | Tested for ability to gel quickly and maintain this form with culture medium for a period of 14 days at 37°C. | PASS |
| Biological Activity | Biological activity is determined using a neurite outgrowth assay. Chick dorsal root ganglia are plated on a 1.0 mm layer of Corning Matrigel Matrix. Tested for a positive neurite outgrowth response after 48 hours without addition of nerve growth factor. | PASS |
| Sterility | Tested for the presence of bacteria, fungi and mycoplasma. | NEGATIVE |
| MAP Test | Mouse colonies screened for Sendai, MHV, PVM, TEMV/GDVII, Ectro, Polyoma, MRV/EDIM, LCM, MCMV, M.Ad, Reo, MPV, LDEV/LDHV, MTV, Hantaan, K, RCMV, CARB | NEGATIVE |
| PCR Test | Tumor source tested for <i>Mycoplasma spp.</i> , <i>Helicobacter</i> , LDEV/LDHV, Sendai, MHV, PVM, MMV/MVM, MPV, Reo (1, 2, 3), MRV/EDIM, Ectro, LCM, K, MTV, Polyoma, Hantaan, Seoul, M. Ad (1, 2), MCMV, Norovirus, TMEV/GDVII, KRV, Toolan's H-1, RCV/SDA Finished goods tested for LDEV/LDHV. | NEGATIVE |

SAFETY RECOMMENDATION: Handle in accordance with good industrial hygiene and laboratory safety practices

Expiration Date: December 7, 2021

Quality Assurance



Date

November 25, 2019

Discovery Labware, Inc., Two Oak Park, Bedford, MA 01730, Tel: 1.978.442.2200 (U.S.)
CLSTechServ@Corning.com www.corning.com/lifesciences

CORNING

For Research Use Only. Not for use in diagnostic or therapeutic procedures.

For a listing of trademarks, visit www.corning.com/lifesciences/trademarks

© 2013 Corning Incorporated

All other trademarks in this document are the property of their respective owners.